



Flange dimensions according to ISO 9409

CM No.#	Conjunction Plate	Applicability By Ratio						Dimension												
		4	5	7	10	14	20	C1	C2	C3	C4	C5	C6	C7	C8	C9	C10	C11	X1	X2
CM1	11L30□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	11S30□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	17L30□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	17S30□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	23L20□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
CM2	23S30□	-	-	-	-	-	-	66.675	4-M4x9	14 std 16 max	35.5	38.15	4	58	18.5	116	13	81	8	75
	56B10□	-	-	-	-	-	-	-	-		-	-	-	-	-	-	-	-	-	-
	56B20□	-	-	-	-	-	-	-	-		-	-	-	-	-	-	-	-	-	-
	60A10□	-	-	-	-	-	-	70	4-M5x10		36	50	8	60	19	116.5	13.5	81.5	8.5	79
	60A20□	-	-	-	-	-	-	-	-		-	-	-	-	-	-	-	-	-	-
60A40□	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	

Date	2014.05.12 (2008.04.21/2011.05.19)	Title	Cool Muscle Gear 1-stage CM-ADR064
Scale	1 : 1	Dwg No.	CMADR0641-30
Size	A2		
3RD Angle Projection			